

Manual Button Battery Sealing Machine

货号: PC2N



简介

The manual button battery sealing machine is a high-precision packaging device designed specifically for small button batteries (such as CR2032, LR44 and other models). It is suitable for laboratory research and development, small batch production and teaching demonstrations.

[了解更多](#)

Instrument model	PC-2N
Pressure range	0-2T (0-25MPa)
Piston diameter	32mm(d) in chrome-plated oil cylinder
Pressure gauge	Dual scale display of pressure and pressure
Standard mold	Standard CR20 series package mold
Sealing mold	Optional CR16, CR20, CR24, CR30, etc.
Sealing pressure	Generally between 0.8-1.2 tons
Shell removal mold	Optional CR16, CR20, CR24, CR30, etc.
Shell removal pressure	Generally within 0.4 tons
Overall dimensions	210*165*290mm(LX*W*H)
Equipment weight	12Kg
Machine size diagram	